

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266618

Luminaire Tested: P3AS05R259735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 239.0 lumens
Efficiency: N/A
Efficacy: 33.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266618

CATALOG NUMBER: P3AS05R259735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266618

CATALOG NUMBER: P3AS05R259735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153299
5°	143033
10°	114583
15°	77776
20°	47067
25°	27510
30°	15673
35°	8620
40°	4580
45°	2419
50°	1399
55°	1032
60°	921
65°	934
70°	898
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2419 cd/sqm

TEST NUMBER: P1266618

CATALOG NUMBER: P3AS05R259735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	24.1
10°-20°	94.2	39.4
20°-30°	53.8	22.5
30°-40°	21.2	8.9
40°-50°	6.5	2.7
50°-60°	2.6	1.1
60°-70°	1.7	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.7	86.1
0°-40°	226.9	94.9
0°-60°	236.0	98.7
0°-90°	239.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	239.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	699	
5°	650	58
15°	343	94
25°	114	54
35°	32	21
45°	8	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266618

CATALOG NUMBER: P3AS05R259735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	699.1
1°	697.8
2°	692.1
3°	682.0
4°	668.1
5°	649.8
6°	628.3
7°	604.1
8°	576.0
9°	547.3
10°	514.6
11°	482.4
12°	447.0
13°	412.0
14°	376.2
15°	342.6
17.5°	265.6
20°	201.7
22.5°	151.4
25°	113.7
27.5°	84.3
30°	61.9
32.5°	44.8
35°	32.2
37.5°	22.8
40°	16.0
42.5°	11.0
45°	7.8
47.5°	5.5
50°	4.1
52.5°	3.2
55°	2.7
57.5°	2.5
60°	2.1
62.5°	1.8
65°	1.8
67.5°	1.6
70°	1.4
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.2



TEST NUMBER: P1266618

CATALOG NUMBER: P3AS05R259735DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)