

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265794

Luminaire Tested: P3AS20R309730D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265794
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309730D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1235.0 lumens
Efficiency: N/A
Efficacy: 42.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265794

CATALOG NUMBER: P3AS20R309730D010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265794

CATALOG NUMBER: P3AS20R309730D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	291775
5°	285207
10°	265237
15°	236006
20°	202994
25°	171978
30°	142756
35°	111976
40°	80265
45°	52626
50°	29986
55°	19689
60°	18595
65°	17278
70°	15515
75°	14149
80°	13386
85°	11322

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 52626 cd/sqm

TEST NUMBER: P1265794

CATALOG NUMBER: P3AS20R309730D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	9.7
10°-20°	289.0	23.4
20°-30°	325.7	26.4
30°-40°	260.1	21.1
40°-50°	133.7	10.8
50°-60°	50.3	4.1
60°-70°	33.0	2.7
70°-80°	17.8	1.4
80°-90°	5.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	735.0	59.5
0°-40°	995.1	80.6
0°-60°	1179.1	95.5
0°-90°	1235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1235.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1331	
5°	1296	120
15°	1040	289
25°	711	326
35°	418	260
45°	170	134
55°	52	50
65°	33	33
75°	17	18
85°	4	5
90°	0	

TEST NUMBER: P1265794

CATALOG NUMBER: P3AS20R309730D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1330.6
1°	1330.6
2°	1326.0
3°	1318.5
4°	1307.8
5°	1295.7
6°	1280.6
7°	1260.9
8°	1239.7
9°	1215.4
10°	1191.2
11°	1163.9
12°	1135.1
13°	1104.8
14°	1073.0
15°	1039.6
17.5°	954.7
20°	869.9
22.5°	788.0
25°	710.8
27.5°	635.0
30°	563.8
32.5°	491.0
35°	418.3
37.5°	347.0
40°	280.4
42.5°	221.3
45°	169.7
47.5°	125.8
50°	87.9
52.5°	62.1
55°	51.5
57.5°	47.0
60°	42.4
62.5°	37.9
65°	33.3
67.5°	28.8
70°	24.2
72.5°	19.7
75°	16.7
77.5°	13.6
80°	10.6
82.5°	7.6
85°	4.5
87.5°	1.5



TEST NUMBER: P1265794

CATALOG NUMBER: P3AS20R309730D010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)