

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266681

Luminaire Tested: P3AS05R359735DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359735DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 490.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266681
CATALOG NUMBER: P3AS05R359735DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1266681

CATALOG NUMBER: P3AS05R359735DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	247129
5°	237508
10°	206943
15°	158503
20°	106036
25°	64165
30°	36816
35°	20586
40°	10935
45°	5644
50°	2695
55°	2141
60°	2061
65°	1712
70°	1795
75°	1610
80°	1768
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5644 cd/sqm



TEST NUMBER: P1266681
 CATALOG NUMBER: P3AS05R359735DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.2	20.0
10°-20°	190.2	38.8
20°-30°	124.5	25.4
30°-40°	50.5	10.3
40°-50°	15.2	3.1
50°-60°	5.2	1.1
60°-70°	3.5	0.7
70°-80°	2.0	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.0	84.3
0°-40°	463.5	94.6
0°-60°	483.8	98.7
0°-90°	490.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	490.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1127	
5°	1079	98
15°	698	190
25°	265	125
35°	77	51
45°	18	15
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1266681
CATALOG NUMBER: P3AS05R359735DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1127.0
1°	1125.2
2°	1120.0
3°	1109.8
4°	1097.7
5°	1079.0
6°	1055.7
7°	1029.6
8°	1000.2
9°	966.7
10°	929.4
11°	887.9
12°	844.6
13°	796.1
14°	750.0
15°	698.2
17.5°	572.8
20°	454.4
22.5°	349.6
25°	265.2
27.5°	197.6
30°	145.4
32.5°	106.7
35°	76.9
37.5°	54.5
40°	38.2
42.5°	26.6
45°	18.2
47.5°	12.1
50°	7.9
52.5°	6.1
55°	5.6
57.5°	5.1
60°	4.7
62.5°	4.2
65°	3.3
67.5°	2.8
70°	2.8
72.5°	2.3
75°	1.9
77.5°	1.4
80°	1.4
82.5°	0.9
85°	0.5
87.5°	0.5



TEST NUMBER: P1266681
CATALOG NUMBER: P3AS05R359735DE010 E3DL1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)