

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266684

Luminaire Tested: P3AS05R359735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 185.0 lumens
Efficiency: N/A
Efficacy: 25.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266684
CATALOG NUMBER: P3AS05R359735DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1266684
 CATALOG NUMBER: P3AS05R359735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42255
5°	41360
10°	38743
15°	34779
20°	30243
25°	25768
30°	21598
35°	17186
40°	12423
45°	7877
50°	4298
55°	2982
60°	2807
65°	2594
70°	2500
75°	2118
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7877 cd/sqm



TEST NUMBER: P1266684
 CATALOG NUMBER: P3AS05R359735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.5	9.5
10°-20°	42.6	23.0
20°-30°	48.8	26.4
30°-40°	39.9	21.5
40°-50°	20.1	10.9
50°-60°	7.5	4.0
60°-70°	5.0	2.7
70°-80°	2.8	1.5
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.0	58.9
0°-40°	148.8	80.4
0°-60°	176.4	95.3
0°-90°	185.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	185.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	193	
5°	188	17
15°	153	43
25°	106	49
35°	64	40
45°	25	20
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1266684
CATALOG NUMBER: P3AS05R359735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	192.7
1°	192.5
2°	192.0
3°	191.1
4°	189.7
5°	187.9
6°	185.6
7°	183.3
8°	180.4
9°	177.4
10°	174.0
11°	170.3
12°	166.4
13°	162.1
14°	157.5
15°	153.2
17.5°	141.5
20°	129.6
22.5°	117.5
25°	106.5
27.5°	95.8
30°	85.3
32.5°	74.8
35°	64.2
37.5°	53.7
40°	43.4
42.5°	33.8
45°	25.4
47.5°	18.3
50°	12.6
52.5°	9.1
55°	7.8
57.5°	7.1
60°	6.4
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.9
72.5°	3.2
75°	2.5
77.5°	2.1
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.5



TEST NUMBER: P1266684
CATALOG NUMBER: P3AS05R359735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)