

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265862

Luminaire Tested: P3AS20R459730D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459730D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2031.9 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265862

CATALOG NUMBER: P3AS20R459730D010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1265862

CATALOG NUMBER: P3AS20R459730D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	91	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		88	86	84	83
5	98	91	86	82	96	90	85	82	88	84	81		87	83	81		85	82	80	79
6	94	87	82	78	93	86	81	78	85	80	77		83	80	77		82	79	76	75
7	90	83	78	74	89	82	78	74	81	77	74		80	76	74		79	76	73	72
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	880982
5°	885690
10°	858457
15°	719391
20°	549921
25°	334785
30°	139287
35°	44624
40°	13883
45°	2822
50°	2081
55°	2332
60°	1974
65°	2335
70°	1923
75°	2542
80°	1894
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2822 cd/sqm

TEST NUMBER: P1265862

CATALOG NUMBER: P3AS20R459730D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.5	18.7
10°-20°	871.0	42.9
20°-30°	627.1	30.9
30°-40°	130.5	6.4
40°-50°	11.9	0.6
50°-60°	4.9	0.2
60°-70°	3.9	0.2
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1877.5	92.4
0°-40°	2008.0	98.8
0°-60°	2024.9	99.7
0°-90°	2031.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2031.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4018	
5°	4024	379
15°	3169	871
25°	1384	627
35°	167	130
45°	9	12
55°	6	5
65°	4	4
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1265862

CATALOG NUMBER: P3AS20R459730D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4017.6
2.5°	4019.1
5°	4023.7
7.5°	3994.9
10°	3855.4
12.5°	3564.5
15°	3168.9
17.5°	2764.3
20°	2356.6
22.5°	1888.3
25°	1383.7
27.5°	912.3
30°	550.1
32.5°	307.6
35°	166.7
37.5°	94.0
40°	48.5
42.5°	21.2
45°	9.1
47.5°	6.1
50°	6.1
52.5°	6.1
55°	6.1
57.5°	4.5
60°	4.5
62.5°	4.5
65°	4.5
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)