

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265895

Luminaire Tested: P3AS20R509730D010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265895  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R509730D010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2105.0 lumens  
Efficiency: N/A  
Efficacy: 73.1 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265895  
CATALOG NUMBER: P3AS20R509730D010 E3D1WH

### Luminous Intensity Polar Plot







TEST NUMBER: P1265895  
 CATALOG NUMBER: P3AS20R509730D010 E3D1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 304.7  | 14.5      |
| 10°-20°   | 755.0  | 35.9      |
| 20°-30°   | 793.6  | 37.7      |
| 30°-40°   | 227.1  | 10.8      |
| 40°-50°   | 22.2   | 1.1       |
| 50°-60°   | 1.8    | 0.1       |
| 60°-70°   | 0.6    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1853.3 | 88.0      |
| 0°-40°    | 2080.4 | 98.8      |
| 0°-60°    | 2104.4 | 100.0     |
| 0°-90°    | 2105.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2105.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3355 |      |
| 5°  | 3253 | 305  |
| 15° | 2725 | 755  |
| 25° | 1814 | 794  |
| 35° | 293  | 227  |
| 45° | 24   | 22   |
| 55° | 2    | 2    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1265895  
CATALOG NUMBER: P3AS20R509730D010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3354.7 |
| 1°    | 3349.5 |
| 2°    | 3334.6 |
| 3°    | 3313.1 |
| 4°    | 3284.1 |
| 5°    | 3252.9 |
| 6°    | 3219.5 |
| 7°    | 3183.9 |
| 8°    | 3150.4 |
| 9°    | 3111.8 |
| 10°   | 3068.7 |
| 11°   | 3019.0 |
| 12°   | 2961.8 |
| 13°   | 2890.5 |
| 14°   | 2813.3 |
| 15°   | 2724.9 |
| 16°   | 2631.3 |
| 17°   | 2540.7 |
| 18°   | 2447.9 |
| 19°   | 2366.2 |
| 20°   | 2293.4 |
| 21°   | 2223.6 |
| 22°   | 2144.1 |
| 23°   | 2052.8 |
| 24°   | 1945.8 |
| 25°   | 1814.4 |
| 26°   | 1671.8 |
| 27°   | 1512.8 |
| 28°   | 1354.6 |
| 29°   | 1183.8 |
| 30°   | 995.9  |
| 31°   | 819.9  |
| 32°   | 658.0  |
| 32.5° | 587.5  |
| 33°   | 516.2  |
| 34°   | 395.8  |
| 35°   | 292.6  |
| 36°   | 214.6  |
| 37°   | 159.7  |
| 37.5° | 138.1  |
| 38°   | 119.6  |
| 39°   | 92.8   |
| 40°   | 73.5   |
| 42.5° | 41.6   |
| 45°   | 23.8   |



TEST NUMBER: P1265895  
CATALOG NUMBER: P3AS20R509730D010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

|       | 0°   |
|-------|------|
| 47.5° | 13.4 |
| 50°   | 5.2  |
| 52.5° | 2.2  |
| 55°   | 1.5  |
| 57.5° | 1.5  |
| 60°   | 0.7  |
| 62.5° | 0.7  |
| 65°   | 0.7  |
| 67.5° | 0.7  |
| 70°   | 0.0  |
| 72.5° | 0.0  |
| 75°   | 0.0  |
| 77.5° | 0.0  |
| 80°   | 0.0  |
| 82.5° | 0.0  |
| 85°   | 0.0  |
| 87.5° | 0.0  |
| 90°   | 0.0  |

(END OF REPORT)