

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265932

Luminaire Tested: P3AS20R559730D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559730D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 629.0 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265932

CATALOG NUMBER: P3AS20R559730D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265932

CATALOG NUMBER: P3AS20R559730D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118258
5°	116751
10°	112156
15°	104904
20°	95698
25°	85384
30°	74670
35°	62051
40°	48920
45°	33182
50°	20264
55°	10513
60°	9780
65°	9236
70°	8591
75°	7540
80°	7450
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33182 cd/sqm

TEST NUMBER: P1265932

CATALOG NUMBER: P3AS20R559730D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	7.9
10°-20°	129.2	20.5
20°-30°	161.7	25.7
30°-40°	144.4	23.0
40°-50°	84.5	13.4
50°-60°	29.2	4.6
60°-70°	17.6	2.8
70°-80°	9.8	1.6
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.6	54.2
0°-40°	485.0	77.1
0°-60°	598.7	95.2
0°-90°	629.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	629.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	539	
5°	530	50
15°	462	129
25°	353	162
35°	232	144
45°	107	85
55°	28	29
65°	18	18
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1265932

CATALOG NUMBER: P3AS20R559730D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	539.3
2.5°	536.4
5°	530.4
7.5°	518.5
10°	503.7
12.5°	485.1
15°	462.1
17.5°	437.6
20°	410.1
22.5°	381.9
25°	352.9
27.5°	323.9
30°	294.9
32.5°	263.7
35°	231.8
37.5°	200.6
40°	170.9
42.5°	138.9
45°	107.0
47.5°	81.7
50°	59.4
52.5°	38.6
55°	27.5
57.5°	24.5
60°	22.3
62.5°	20.1
65°	17.8
67.5°	15.6
70°	13.4
72.5°	11.1
75°	8.9
77.5°	7.4
80°	5.9
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)