

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266770

Luminaire Tested: P3AS05R509735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266770
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 200.0 lumens
Efficiency: N/A
Efficacy: 27.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266770

CATALOG NUMBER: P3AS05R509735DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266770

CATALOG NUMBER: P3AS05R509735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40655
5°	40040
10°	38276
15°	35437
20°	31853
25°	27994
30°	23801
35°	19301
40°	14513
45°	9334
50°	4435
55°	3479
60°	3289
65°	3061
70°	2757
75°	2542
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9334 cd/sqm

TEST NUMBER: P1266770

CATALOG NUMBER: P3AS05R509735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.1	8.5
10°-20°	43.5	21.8
20°-30°	52.9	26.4
30°-40°	44.8	22.4
40°-50°	23.3	11.7
50°-60°	8.4	4.2
60°-70°	5.8	2.9
70°-80°	3.2	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	113.5	56.7
0°-40°	158.3	79.2
0°-60°	190.0	95.0
0°-90°	200.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	200.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	185	
5°	182	17
15°	156	44
25°	116	53
35°	72	45
45°	30	23
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1266770

CATALOG NUMBER: P3AS05R509735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	185.4
2.5°	184.7
5°	181.9
7.5°	177.8
10°	171.9
12.5°	164.4
15°	156.1
17.5°	146.8
20°	136.5
22.5°	126.0
25°	115.7
27.5°	105.0
30°	94.0
32.5°	83.1
35°	72.1
37.5°	61.4
40°	50.7
42.5°	40.4
45°	30.1
47.5°	20.1
50°	13.0
52.5°	10.0
55°	9.1
57.5°	8.2
60°	7.5
62.5°	6.6
65°	5.9
67.5°	5.0
70°	4.3
72.5°	3.7
75°	3.0
77.5°	2.3
80°	1.8
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)