

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265940

Luminaire Tested: P3AS20R559730D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559730D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1103.0 lumens
Efficiency: N/A
Efficacy: 38.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265940
CATALOG NUMBER: P3AS20R559730D010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1265940
 CATALOG NUMBER: P3AS20R559730D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	300042
5°	292515
10°	271961
15°	242181
20°	205795
25°	166074
30°	126627
35°	90052
40°	59426
45°	35228
50°	20673
55°	12731
60°	11315
65°	10222
70°	8719
75°	7710
80°	7703
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35228 cd/sqm



TEST NUMBER: P1265940
 CATALOG NUMBER: P3AS20R559730D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	11.2
10°-20°	295.8	26.8
20°-30°	313.2	28.4
30°-40°	211.7	19.2
40°-50°	92.8	8.4
50°-60°	33.2	3.0
60°-70°	19.5	1.8
70°-80°	10.2	0.9
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	732.4	66.4
0°-40°	944.1	85.6
0°-60°	1070.0	97.0
0°-90°	1103.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1103.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1368	
5°	1329	123
15°	1067	296
25°	686	313
35°	336	212
45°	114	93
55°	33	33
65°	20	19
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P1265940
CATALOG NUMBER: P3AS20R559730D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1368.3
2.5°	1357.7
5°	1328.9
7.5°	1282.0
10°	1221.4
12.5°	1148.6
15°	1066.8
17.5°	975.9
20°	881.9
22.5°	783.4
25°	686.4
27.5°	591.0
30°	500.1
32.5°	413.7
35°	336.4
37.5°	266.7
40°	207.6
42.5°	156.1
45°	113.6
47.5°	83.3
50°	60.6
52.5°	42.4
55°	33.3
57.5°	30.3
60°	25.8
62.5°	22.7
65°	19.7
67.5°	16.7
70°	13.6
72.5°	12.1
75°	9.1
77.5°	7.6
80°	6.1
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)