

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265950

Luminaire Tested: P3AS20R609730D010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609730D010 E3D1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1815.9 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265950
CATALOG NUMBER: P3AS20R609730D010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1265950
 CATALOG NUMBER: P3AS20R609730D010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	475817
5°	449173
10°	437511
15°	427517
20°	397495
25°	355327
30°	271434
35°	156707
40°	60828
45°	25336
50°	5561
55°	841
60°	658
65°	363
70°	449
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25336 cd/sqm



TEST NUMBER: P1265950
 CATALOG NUMBER: P3AS20R609730D010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.6	10.6
10°-20°	524.6	28.9
20°-30°	657.0	36.2
30°-40°	367.3	20.2
40°-50°	69.8	3.8
50°-60°	3.6	0.2
60°-70°	0.8	0.0
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1374.2	75.7
0°-40°	1741.5	95.9
0°-60°	1814.9	99.9
0°-90°	1815.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1815.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2170	
5°	2041	193
15°	1883	525
25°	1469	657
35°	585	367
45°	82	70
55°	2	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1265950
CATALOG NUMBER: P3AS20R609730D010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2169.9
1°	2161.0
2°	2132.8
3°	2099.3
4°	2068.1
5°	2040.6
6°	2019.8
7°	2002.0
8°	1988.6
9°	1976.0
10°	1964.9
11°	1953.7
12°	1941.1
13°	1925.5
14°	1906.9
15°	1883.2
16°	1854.2
17°	1821.5
18°	1784.4
19°	1742.0
20°	1703.4
21°	1661.8
22°	1618.7
23°	1573.4
24°	1523.6
25°	1468.6
26°	1404.0
27°	1332.0
28°	1251.0
29°	1164.8
30°	1072.0
31°	978.3
32°	881.8
32.5°	829.0
33°	781.5
34°	682.7
35°	585.4
36°	497.7
37°	404.9
37.5°	362.5
38°	320.9
39°	258.5
40°	212.5
42.5°	129.3
45°	81.7



TEST NUMBER: P1265950
CATALOG NUMBER: P3AS20R609730D010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	45.3
50°	16.3
52.5°	3.7
55°	2.2
57.5°	1.5
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)