

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265955

Luminaire Tested: P3AS20R609730D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265955
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609730D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 781.0 lumens
Efficiency: N/A
Efficacy: 27.1 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265955

CATALOG NUMBER: P3AS20R609730D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265955

CATALOG NUMBER: P3AS20R609730D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184415
5°	182676
10°	177351
15°	166153
20°	147059
25°	123031
30°	96420
35°	69948
40°	46544
45°	28995
50°	15692
55°	4549
60°	4210
65°	3840
70°	3783
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28995 cd/sqm

TEST NUMBER: P1265955

CATALOG NUMBER: P3AS20R609730D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.1	10.0
10°-20°	203.1	26.0
20°-30°	231.4	29.6
30°-40°	164.1	21.0
40°-50°	74.5	9.5
50°-60°	15.8	2.0
60°-70°	7.6	1.0
70°-80°	4.7	0.6
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	512.6	65.6
0°-40°	676.8	86.7
0°-60°	767.0	98.2
0°-90°	781.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	781.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	841	
5°	830	78
15°	732	203
25°	508	231
35°	261	164
45°	94	74
55°	12	16
65°	7	8
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1265955

CATALOG NUMBER: P3AS20R609730D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	841.0
2.5°	838.1
5°	829.9
7.5°	815.8
10°	796.5
12.5°	769.0
15°	731.9
17.5°	685.1
20°	630.2
22.5°	570.8
25°	508.5
27.5°	444.6
30°	380.8
32.5°	319.9
35°	261.3
37.5°	209.3
40°	162.6
42.5°	123.2
45°	93.5
47.5°	69.8
50°	46.0
52.5°	21.5
55°	11.9
57.5°	10.4
60°	9.6
62.5°	8.9
65°	7.4
67.5°	6.7
70°	5.9
72.5°	5.2
75°	4.5
77.5°	3.7
80°	3.0
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)