

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266780

Luminaire Tested: P3AS05R509735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 525.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266780

CATALOG NUMBER: P3AS05R509735DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1266780

CATALOG NUMBER: P3AS05R509735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167158
5°	163790
10°	153415
15°	137345
20°	115580
25°	88215
30°	57325
35°	33997
40°	19637
45°	9830
50°	3650
55°	2867
60°	2675
65°	2439
70°	2372
75°	2372
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9830 cd/sqm

TEST NUMBER: P1266780

CATALOG NUMBER: P3AS05R509735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	13.2
10°-20°	167.3	31.9
20°-30°	164.1	31.3
30°-40°	82.7	15.8
40°-50°	26.1	5.0
50°-60°	6.8	1.3
60°-70°	4.8	0.9
70°-80°	3.0	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	400.7	76.3
0°-40°	483.4	92.1
0°-60°	516.2	98.3
0°-90°	525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	762	
5°	744	69
15°	605	167
25°	365	164
35°	127	83
45°	32	26
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1266780

CATALOG NUMBER: P3AS05R509735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	762.3
2.5°	757.6
5°	744.1
7.5°	719.8
10°	689.0
12.5°	649.3
15°	605.0
17.5°	553.6
20°	495.3
22.5°	432.2
25°	364.6
27.5°	292.7
30°	226.4
32.5°	170.4
35°	127.0
37.5°	93.8
40°	68.6
42.5°	48.5
45°	31.7
47.5°	18.2
50°	10.7
52.5°	7.9
55°	7.5
57.5°	6.5
60°	6.1
62.5°	5.6
65°	4.7
67.5°	4.2
70°	3.7
72.5°	3.3
75°	2.8
77.5°	2.3
80°	1.9
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)