

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265958

Luminaire Tested: P3AS20R609730D010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609730D010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1594.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265958
CATALOG NUMBER: P3AS20R609730D010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265958
 CATALOG NUMBER: P3AS20R609730D010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73				73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	376395
5°	372836
10°	361962
15°	339117
20°	300139
25°	251095
30°	196790
35°	142760
40°	94978
45°	59200
50°	32033
55°	9252
60°	8640
65°	7887
70°	7758
75°	7710
80°	7703
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 59200 cd/sqm



TEST NUMBER: P1265958
 CATALOG NUMBER: P3AS20R609730D010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.5	10.0
10°-20°	414.4	26.0
20°-30°	472.4	29.6
30°-40°	335.0	21.0
40°-50°	152.0	9.5
50°-60°	32.2	2.0
60°-70°	15.6	1.0
70°-80°	9.6	0.6
80°-90°	3.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.3	65.6
0°-40°	1381.3	86.7
0°-60°	1565.5	98.2
0°-90°	1594.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1594.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1716	
5°	1694	159
15°	1494	414
25°	1038	472
35°	533	335
45°	191	152
55°	24	32
65°	15	16
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P1265958
CATALOG NUMBER: P3AS20R609730D010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1716.5
2.5°	1710.4
5°	1693.8
7.5°	1665.0
10°	1625.6
12.5°	1569.5
15°	1493.8
17.5°	1398.3
20°	1286.2
22.5°	1165.0
25°	1037.8
27.5°	907.5
30°	777.2
32.5°	653.0
35°	533.3
37.5°	427.2
40°	331.8
42.5°	251.5
45°	190.9
47.5°	142.4
50°	93.9
52.5°	43.9
55°	24.2
57.5°	21.2
60°	19.7
62.5°	18.2
65°	15.2
67.5°	13.6
70°	12.1
72.5°	10.6
75°	9.1
77.5°	7.6
80°	6.1
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)