

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265973

Luminaire Tested: P3AS20R659730D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659730D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1875.0 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265973

CATALOG NUMBER: P3AS20R659730D010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1265973

CATALOG NUMBER: P3AS20R659730D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	458209
5°	431256
10°	425777
15°	418254
20°	394904
25°	366529
30°	284905
35°	164818
40°	66410
45°	30577
50°	11906
55°	4626
60°	3991
65°	3943
70°	3911
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30577 cd/sqm

TEST NUMBER: P1265973

CATALOG NUMBER: P3AS20R659730D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.2	9.9
10°-20°	514.5	27.4
20°-30°	673.5	35.9
30°-40°	390.1	20.8
40°-50°	83.5	4.5
50°-60°	13.6	0.7
60°-70°	7.5	0.4
70°-80°	4.4	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1374.3	73.3
0°-40°	1764.4	94.1
0°-60°	1861.5	99.3
0°-90°	1875.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1875.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2090	
5°	1959	186
15°	1842	515
25°	1515	674
35°	616	390
45°	99	84
55°	12	14
65°	8	8
75°	4	4
85°	2	2
90°	0	

TEST NUMBER: P1265973

CATALOG NUMBER: P3AS20R659730D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2089.6
2.5°	2030.5
5°	1959.2
7.5°	1930.4
10°	1912.2
12.5°	1886.4
15°	1842.4
17.5°	1774.2
20°	1692.3
22.5°	1615.0
25°	1514.9
27.5°	1346.6
30°	1125.2
32.5°	871.9
35°	615.7
37.5°	389.7
40°	232.0
42.5°	145.6
45°	98.6
47.5°	63.7
50°	34.9
52.5°	16.7
55°	12.1
57.5°	10.6
60°	9.1
62.5°	9.1
65°	7.6
67.5°	6.1
70°	6.1
72.5°	4.5
75°	4.5
77.5°	3.0
80°	3.0
82.5°	1.5
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)