

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266841

Luminaire Tested: P3AS05R659735DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266841
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659735DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 577.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266841

CATALOG NUMBER: P3AS05R659735DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1266841

CATALOG NUMBER: P3AS05R659735DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140997
5°	132709
10°	131015
15°	128718
20°	121531
25°	112797
30°	87684
35°	50728
40°	20438
45°	9396
50°	3650
55°	1415
60°	1228
65°	1193
70°	1218
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9396 cd/sqm

TEST NUMBER: P1266841

CATALOG NUMBER: P3AS05R659735DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.3	9.9
10°-20°	158.3	27.4
20°-30°	207.3	35.9
30°-40°	120.1	20.8
40°-50°	25.7	4.5
50°-60°	4.2	0.7
60°-70°	2.3	0.4
70°-80°	1.3	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.9	73.3
0°-40°	543.0	94.1
0°-60°	572.8	99.3
0°-90°	577.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	577.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	643	
5°	603	57
15°	567	158
25°	466	207
35°	190	120
45°	30	26
55°	4	4
65°	2	2
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P1266841

CATALOG NUMBER: P3AS05R659735DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	643.0
2.5°	624.8
5°	602.9
7.5°	594.0
10°	588.4
12.5°	580.5
15°	567.0
17.5°	546.0
20°	520.8
22.5°	497.0
25°	466.2
27.5°	414.4
30°	346.3
32.5°	268.3
35°	189.5
37.5°	119.9
40°	71.4
42.5°	44.8
45°	30.3
47.5°	19.6
50°	10.7
52.5°	5.1
55°	3.7
57.5°	3.3
60°	2.8
62.5°	2.8
65°	2.3
67.5°	1.9
70°	1.9
72.5°	1.4
75°	1.4
77.5°	0.9
80°	0.9
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)