

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266860

Luminaire Tested: P3AS05R659735DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266860
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659735DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 367.0 lumens
Efficiency: N/A
Efficacy: 51.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266860
CATALOG NUMBER: P3AS05R659735DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1266860
 CATALOG NUMBER: P3AS05R659735DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65302
5°	64429
10°	62279
15°	58729
20°	54161
25°	49164
30°	43551
35°	37049
40°	29484
45°	20808
50°	12076
55°	6576
60°	6140
65°	5552
70°	5065
75°	4745
80°	4167
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20808 cd/sqm



TEST NUMBER: P1266860
 CATALOG NUMBER: P3AS05R659735DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.5	7.5
10°-20°	72.4	19.7
20°-30°	93.0	25.3
30°-40°	86.0	23.4
40°-50°	51.9	14.2
50°-60°	17.7	4.8
60°-70°	10.6	2.9
70°-80°	6.0	1.6
80°-90°	1.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.9	52.6
0°-40°	278.9	76.0
0°-60°	348.6	95.0
0°-90°	367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	367.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	298	
5°	293	28
15°	259	72
25°	203	93
35°	138	86
45°	67	52
55°	17	18
65°	11	11
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1266860
CATALOG NUMBER: P3AS05R659735DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	297.8
2.5°	296.4
5°	292.7
7.5°	287.1
10°	279.7
12.5°	270.3
15°	258.7
17.5°	246.1
20°	232.1
22.5°	217.7
25°	203.2
27.5°	187.8
30°	172.0
32.5°	156.1
35°	138.4
37.5°	121.2
40°	103.0
42.5°	84.8
45°	67.1
47.5°	50.8
50°	35.4
52.5°	22.4
55°	17.2
57.5°	15.4
60°	14.0
62.5°	12.1
65°	10.7
67.5°	9.3
70°	7.9
72.5°	7.0
75°	5.6
77.5°	4.7
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0

(END OF REPORT)