

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265999

Luminaire Tested: P3AS20R659730D010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659730D010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1050.0 lumens
Efficiency: N/A
Efficacy: 36.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265999
CATALOG NUMBER: P3AS20R659730D010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265999

CATALOG NUMBER: P3AS20R659730D010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	266887
5°	260246
10°	242369
15°	217186
20°	187570
25°	156033
30°	123032
35°	91176
40°	62832
45°	38950
50°	21185
55°	13304
60°	11271
65°	10222
70°	8719
75°	7710
80°	7703
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38950 cd/sqm



TEST NUMBER: P1265999
 CATALOG NUMBER: P3AS20R659730D010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	10.5
10°-20°	265.9	25.3
20°-30°	294.0	28.0
30°-40°	213.6	20.3
40°-50°	100.0	9.5
50°-60°	33.7	3.2
60°-70°	19.5	1.9
70°-80°	10.2	1.0
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.8	63.8
0°-40°	883.3	84.1
0°-60°	1017.0	96.9
0°-90°	1050.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1050.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1217	
5°	1182	110
15°	957	266
25°	645	294
35°	341	214
45°	126	100
55°	35	34
65°	20	19
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P1265999

CATALOG NUMBER: P3AS20R659730D010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1217.1
2.5°	1209.6
5°	1182.3
7.5°	1141.4
10°	1088.5
12.5°	1026.4
15°	956.7
17.5°	881.1
20°	803.8
22.5°	723.6
25°	644.9
27.5°	564.7
30°	485.9
32.5°	410.3
35°	340.6
37.5°	277.0
40°	219.5
42.5°	168.0
45°	125.6
47.5°	90.8
50°	62.1
52.5°	42.4
55°	34.8
57.5°	30.3
60°	25.7
62.5°	22.7
65°	19.7
67.5°	16.7
70°	13.6
72.5°	12.1
75°	9.1
77.5°	7.6
80°	6.1
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)