

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266879

Luminaire Tested: P3AS05R709735DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266879
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709735DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266879

CATALOG NUMBER: P3AS05R709735DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266879

CATALOG NUMBER: P3AS05R709735DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108105
5°	101937
10°	96658
15°	94915
20°	91498
25°	86255
30°	85633
35°	74579
40°	48233
45°	22793
50°	3207
55°	268
60°	219
65°	259
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22793 cd/sqm

TEST NUMBER: P1266879

CATALOG NUMBER: P3AS05R709735DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.2	7.8
10°-20°	117.4	21.1
20°-30°	166.1	29.9
30°-40°	166.9	30.0
40°-50°	60.0	10.8
50°-60°	1.6	0.3
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.8	58.8
0°-40°	493.7	88.8
0°-60°	555.4	99.9
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	493	
5°	463	43
15°	418	117
25°	356	166
35°	279	167
45°	74	60
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266879

CATALOG NUMBER: P3AS05R709735DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	493.0
1°	491.7
2°	487.3
3°	480.5
4°	471.8
5°	463.1
6°	454.9
7°	448.5
8°	442.8
9°	438.2
10°	434.1
11°	430.7
12°	427.5
13°	424.3
14°	421.3
15°	418.1
16°	414.2
17°	410.1
18°	405.1
19°	398.9
20°	392.1
21°	384.6
22°	377.0
23°	369.7
24°	362.6
25°	356.5
26°	352.1
27°	348.7
28°	346.0
29°	342.8
30°	338.2
31°	331.6
32°	322.2
32.5°	317.0
33°	309.9
34°	296.0
35°	278.6
36°	259.4
37°	237.7
37.5°	227.7
38°	214.0
39°	189.5
40°	168.5
42.5°	116.7
45°	73.5



TEST NUMBER: P1266879

CATALOG NUMBER: P3AS05R709735DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	39.5
50°	9.4
52.5°	1.1
55°	0.7
57.5°	0.7
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)