

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266019

Luminaire Tested: P3AS20R709730D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709730D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 534.0 lumens
Efficiency: N/A
Efficacy: 18.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266019

CATALOG NUMBER: P3AS20R709730D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266019

CATALOG NUMBER: P3AS20R709730D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125253
5°	122958
10°	115941
15°	105222
20°	92035
25°	77642
30°	63579
35°	49309
40°	35295
45°	22359
50°	11155
55°	6805
60°	5877
65°	5396
70°	4744
75°	4406
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22359 cd/sqm

TEST NUMBER: P1266019

CATALOG NUMBER: P3AS20R709730D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	9.8
10°-20°	129.0	24.2
20°-30°	146.9	27.5
30°-40°	114.9	21.5
40°-50°	56.4	10.6
50°-60°	17.3	3.2
60°-70°	10.3	1.9
70°-80°	5.5	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.0	61.4
0°-40°	442.8	82.9
0°-60°	516.6	96.7
0°-90°	534.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	534.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	559	52
15°	464	129
25°	321	147
35°	184	115
45°	72	56
55°	18	17
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1266019

CATALOG NUMBER: P3AS20R709730D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	571.2
2.5°	568.2
5°	558.6
7.5°	543.0
10°	520.7
12.5°	494.7
15°	463.5
17.5°	430.1
20°	394.4
22.5°	357.3
25°	320.9
27.5°	285.2
30°	251.1
32.5°	216.9
35°	184.2
37.5°	153.0
40°	123.3
42.5°	95.8
45°	72.1
47.5°	50.5
50°	32.7
52.5°	21.5
55°	17.8
57.5°	15.6
60°	13.4
62.5°	11.9
65°	10.4
67.5°	8.9
70°	7.4
72.5°	5.9
75°	5.2
77.5°	4.5
80°	3.0
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)