

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266092

Luminaire Tested: P3AS02R109735DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109735DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 220.0 lumens
Efficiency: N/A
Efficacy: 57.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266092
CATALOG NUMBER: P3AS02R109735DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1266092

CATALOG NUMBER: P3AS02R109735DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187945
5°	166828
10°	115852
15°	68513
20°	39017
25°	22308
30°	12331
35°	6585
40°	3635
45°	1985
50°	1228
55°	956
60°	833
65°	778
70°	705
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1985 cd/sqm



TEST NUMBER: P1266092
 CATALOG NUMBER: P3AS02R109735DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.4	29.3
10°-20°	85.1	38.7
20°-30°	43.8	19.9
30°-40°	16.4	7.5
40°-50°	5.4	2.5
50°-60°	2.3	1.0
60°-70°	1.5	0.7
70°-80°	0.9	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	193.3	87.9
0°-40°	209.7	95.3
0°-60°	217.4	98.8
0°-90°	220.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	220.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	857	
5°	758	64
15°	302	85
25°	92	44
35°	25	16
45°	6	5
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266092
CATALOG NUMBER: P3AS02R109735DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	857.1
1°	855.4
2°	844.1
3°	822.7
4°	794.5
5°	757.9
6°	716.3
7°	670.8
8°	620.1
9°	570.1
10°	520.3
12.5°	400.3
15°	301.8
17.5°	225.9
20°	167.2
22.5°	124.8
25°	92.2
27.5°	67.2
30°	48.7
32.5°	34.5
35°	24.6
37.5°	17.6
40°	12.7
42.5°	9.1
45°	6.4
47.5°	4.7
50°	3.6
52.5°	3.0
55°	2.5
57.5°	2.1
60°	1.9
62.5°	1.7
65°	1.5
67.5°	1.3
70°	1.1
72.5°	1.1
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)