

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266923

Luminaire Tested: P3AS09R109735DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R109735DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 336.0 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266923

CATALOG NUMBER: P3AS09R109735DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266923

CATALOG NUMBER: P3AS09R109735DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144901
5°	133920
10°	106923
15°	80750
20°	61489
25°	46866
30°	33575
35°	21897
40°	13425
45°	8125
50°	5390
55°	4167
60°	3596
65°	3113
70°	2821
75°	2796
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8125 cd/sqm

TEST NUMBER: P1266923

CATALOG NUMBER: P3AS09R109735DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	16.0
10°-20°	99.4	29.6
20°-30°	88.5	26.3
30°-40°	52.4	15.6
40°-50°	21.5	6.4
50°-60°	10.1	3.0
60°-70°	6.2	1.8
70°-80°	3.2	1.0
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.9	72.0
0°-40°	294.2	87.6
0°-60°	325.8	97.0
0°-90°	336.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	336.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	661	
5°	608	54
15°	356	99
25°	194	89
35°	82	52
45°	26	21
55°	11	10
65°	6	6
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1266923

CATALOG NUMBER: P3AS09R109735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	660.8
1°	659.1
2°	654.2
3°	644.4
4°	628.0
5°	608.4
6°	587.1
7°	562.0
8°	535.8
9°	509.1
10°	480.2
12.5°	414.1
15°	355.7
17.5°	305.6
20°	263.5
22.5°	226.4
25°	193.7
27.5°	162.1
30°	132.6
32.5°	105.9
35°	81.8
37.5°	62.7
40°	46.9
42.5°	34.9
45°	26.2
47.5°	20.2
50°	15.8
52.5°	13.1
55°	10.9
57.5°	9.3
60°	8.2
62.5°	7.1
65°	6.0
67.5°	5.5
70°	4.4
72.5°	3.8
75°	3.3
77.5°	2.2
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)