

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266123

Luminaire Tested: P3AS02R129735DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129735DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 234.0 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266123

CATALOG NUMBER: P3AS02R129735DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1266123

CATALOG NUMBER: P3AS02R129735DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	95		96	94	93
3	106	101	97	93		104	99	96	93		97	94	91		94	92	90		92	90	88
4	102	96	92	88		100	95	91	88		93	89	87		91	88	86		89	87	85
5	98	92	87	84		97	91	87	83		89	85	83		88	84	82		86	83	81
6	95	88	83	80		94	87	83	80		86	82	79		85	81	79		83	80	78
7	92	85	80	77		91	84	80	76		83	79	76		82	78	76		81	78	75
8	89	81	77	74		88	81	77	73		80	76	73		79	75	73		78	75	73
9	86	79	74	71		85	78	74	71		77	73	71		77	73	70		76	73	70
10	84	76	71	68		83	76	71	68		75	71	68		74	71	68		74	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199896
5°	177437
10°	123222
15°	72872
20°	41514
25°	23735
30°	13116
35°	6987
40°	3864
45°	2109
50°	1296
55°	1032
60°	877
65°	830
70°	705
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2109 cd/sqm

TEST NUMBER: P1266123

CATALOG NUMBER: P3AS02R129735DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.5	29.3
10°-20°	90.5	38.7
20°-30°	46.6	19.9
30°-40°	17.5	7.5
40°-50°	5.7	2.5
50°-60°	2.5	1.1
60°-70°	1.6	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.6	87.9
0°-40°	223.1	95.3
0°-60°	231.3	98.8
0°-90°	234.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	234.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	912	
5°	806	69
15°	321	90
25°	98	47
35°	26	17
45°	7	6
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1266123

CATALOG NUMBER: P3AS02R129735DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	911.6
1°	909.8
2°	897.9
3°	875.1
4°	845.1
5°	806.1
6°	761.9
7°	713.5
8°	659.6
9°	606.4
10°	553.4
12.5°	425.8
15°	321.0
17.5°	240.3
20°	177.9
22.5°	132.8
25°	98.1
27.5°	71.5
30°	51.8
32.5°	36.7
35°	26.1
37.5°	18.7
40°	13.5
42.5°	9.7
45°	6.8
47.5°	5.0
50°	3.8
52.5°	3.2
55°	2.7
57.5°	2.3
60°	2.0
62.5°	1.8
65°	1.6
67.5°	1.4
70°	1.1
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)