

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266938

Luminaire Tested: P3AS09R159735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 347.0 lumens
Efficiency: N/A
Efficacy: 31.3 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266938

CATALOG NUMBER: P3AS09R159735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266938

CATALOG NUMBER: P3AS09R159735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	296424
5°	263129
10°	182740
15°	108060
20°	61535
25°	35179
30°	19471
35°	10386
40°	5754
45°	3101
50°	1944
55°	1529
60°	1316
65°	1193
70°	1090
75°	1101
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3101 cd/sqm

TEST NUMBER: P1266938

CATALOG NUMBER: P3AS09R159735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.7	29.3
10°-20°	134.2	38.7
20°-30°	69.1	19.9
30°-40°	25.9	7.5
40°-50°	8.5	2.5
50°-60°	3.6	1.0
60°-70°	2.3	0.7
70°-80°	1.4	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.9	87.9
0°-40°	330.8	95.3
0°-60°	343.0	98.8
0°-90°	347.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	347.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1352	
5°	1195	102
15°	476	134
25°	145	69
35°	39	26
45°	10	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1266938

CATALOG NUMBER: P3AS09R159735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1351.8
1°	1349.2
2°	1331.4
3°	1297.7
4°	1253.2
5°	1195.4
6°	1129.9
7°	1058.0
8°	978.1
9°	899.2
10°	820.7
12.5°	631.5
15°	476.0
17.5°	356.3
20°	263.7
22.5°	196.9
25°	145.4
27.5°	106.0
30°	76.9
32.5°	54.5
35°	38.8
37.5°	27.7
40°	20.1
42.5°	14.4
45°	10.0
47.5°	7.4
50°	5.7
52.5°	4.7
55°	4.0
57.5°	3.3
60°	3.0
62.5°	2.7
65°	2.3
67.5°	2.0
70°	1.7
72.5°	1.7
75°	1.3
77.5°	1.0
80°	0.7
82.5°	0.7
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)