

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266139

Luminaire Tested: P3AS02R159735DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159735DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 287.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266139

CATALOG NUMBER: P3AS02R159735DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1266139

CATALOG NUMBER: P3AS02R159735DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	100	100	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	95	95	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	93	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	92	92	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	90	90	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	89	89	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	87	87	86
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	86	86	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	85	85	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	557850
5°	467531
10°	220236
15°	66402
20°	24572
25°	9557
30°	3570
35°	1098
40°	401
45°	217
50°	171
55°	191
60°	219
65°	104
70°	128
75°	169
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 60°

Luminance: 219 cd/sqm

TEST NUMBER: P1266139

CATALOG NUMBER: P3AS02R159735DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.2	57.2
10°-20°	97.6	34.0
20°-30°	20.5	7.1
30°-40°	3.3	1.2
40°-50°	0.6	0.2
50°-60°	0.4	0.2
60°-70°	0.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.3	98.4
0°-40°	285.6	99.5
0°-60°	286.7	99.9
0°-90°	287.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	287.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2544	
5°	2124	164
15°	292	98
25°	40	21
35°	4	3
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266139

CATALOG NUMBER: P3AS02R159735DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2544.0
1°	2536.1
2°	2495.7
3°	2414.9
4°	2296.5
5°	2124.0
6°	1921.4
7°	1689.8
8°	1468.5
9°	1218.0
10°	989.1
12.5°	533.7
15°	292.5
17.5°	171.3
20°	105.3
22.5°	64.4
25°	39.5
27.5°	23.8
30°	14.1
32.5°	7.9
35°	4.1
37.5°	2.3
40°	1.4
42.5°	0.9
45°	0.7
47.5°	0.5
50°	0.5
52.5°	0.5
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)