

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266958

Luminaire Tested: P3AS09R159735DE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1266958  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R159735DE010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 318.0 lumens  
Efficiency: N/A  
Efficacy: 28.6 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266958  
CATALOG NUMBER: P3AS09R159735DE010 E3PHLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1266958  
 CATALOG NUMBER: P3AS09R159735DE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90	90	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63	63	63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	119026
5°	109289
10°	87084
15°	65086
20°	49424
25°	37430
30°	27675
35°	19782
40°	13540
45°	9458
50°	8051
55°	7914
60°	8201
65°	8665
70°	8848
75°	9150
80°	9976
85°	9812

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 11592 cd/sqm



TEST NUMBER: P1266958

CATALOG NUMBER: P3AS09R159735DE010 E3PHLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	13.8
10°-20°	80.4	25.3
20°-30°	71.2	22.4
30°-40°	46.6	14.7
40°-50°	24.9	7.8
50°-60°	18.9	5.9
60°-70°	16.2	5.1
70°-80°	11.2	3.5
80°-90°	4.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	195.6	61.5
0°-40°	242.3	76.2
0°-60°	286.0	90.0
0°-90°	318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	318.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	543	
5°	496	44
15°	287	80
25°	155	71
35°	74	47
45°	30	25
55°	21	19
65°	17	16
75°	11	11
85°	4	5
90°	0	



TEST NUMBER: P1266958  
CATALOG NUMBER: P3AS09R159735DE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	542.8
2.5°	530.0
5°	496.5
7.5°	447.2
10°	391.1
12.5°	336.9
15°	286.7
17.5°	246.3
20°	211.8
22.5°	181.3
25°	154.7
27.5°	131.0
30°	109.3
32.5°	90.6
35°	73.9
37.5°	59.1
40°	47.3
42.5°	37.4
45°	30.5
47.5°	26.6
50°	23.6
52.5°	22.7
55°	20.7
57.5°	19.7
60°	18.7
62.5°	17.7
65°	16.7
67.5°	14.8
70°	13.8
72.5°	11.8
75°	10.8
77.5°	8.9
80°	7.9
82.5°	6.9
85°	3.9
87.5°	2.0
90°	0.0

(END OF REPORT)