

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266149

Luminaire Tested: P3AS02R159735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 115.0 lumens
Efficiency: N/A
Efficacy: 32.0 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266149

CATALOG NUMBER: P3AS02R159735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266149

CATALOG NUMBER: P3AS02R159735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98238
5°	87211
10°	60564
15°	35823
20°	20395
25°	11662
30°	6457
35°	3453
40°	1889
45°	1023
50°	648
55°	497
60°	439
65°	415
70°	385
75°	339
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1023 cd/sqm

TEST NUMBER: P1266149

CATALOG NUMBER: P3AS02R159735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.7	29.3
10°-20°	44.5	38.7
20°-30°	22.9	19.9
30°-40°	8.6	7.5
40°-50°	2.8	2.4
50°-60°	1.2	1.1
60°-70°	0.8	0.7
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	101.1	87.9
0°-40°	109.7	95.3
0°-60°	113.7	98.8
0°-90°	115.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	115.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	448	
5°	396	34
15°	158	44
25°	48	23
35°	13	9
45°	3	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266149

CATALOG NUMBER: P3AS02R159735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	448.0
1°	447.1
2°	441.3
3°	430.1
4°	415.3
5°	396.2
6°	374.5
7°	350.6
8°	324.2
9°	298.0
10°	272.0
12.5°	209.3
15°	157.8
17.5°	118.1
20°	87.4
22.5°	65.3
25°	48.2
27.5°	35.1
30°	25.5
32.5°	18.1
35°	12.9
37.5°	9.2
40°	6.6
42.5°	4.8
45°	3.3
47.5°	2.4
50°	1.9
52.5°	1.6
55°	1.3
57.5°	1.1
60°	1.0
62.5°	0.9
65°	0.8
67.5°	0.7
70°	0.6
72.5°	0.6
75°	0.4
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.0
90°	0.0

(END OF REPORT)