

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266168

Luminaire Tested: P3AS02R159735DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159735DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 150.0 lumens
Efficiency: N/A
Efficacy: 41.7 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266168
CATALOG NUMBER: P3AS02R159735DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1266168
 CATALOG NUMBER: P3AS02R159735DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90			90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80			80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72			72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66			66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60			60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55			55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51			51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43659
5°	40920
10°	33555
15°	26061
20°	20582
25°	16404
30°	13167
35°	10734
40°	8845
45°	7443
50°	6413
55°	5543
60°	4912
65°	4255
70°	3783
75°	3050
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7443 cd/sqm



TEST NUMBER: P1266168
 CATALOG NUMBER: P3AS02R159735DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.6	11.1
10°-20°	32.2	21.4
20°-30°	31.3	20.8
30°-40°	25.3	16.8
40°-50°	18.8	12.5
50°-60°	13.1	8.8
60°-70°	8.2	5.5
70°-80°	3.9	2.6
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	80.0	53.4
0°-40°	105.3	70.2
0°-60°	137.2	91.5
0°-90°	150.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	150.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	199	
5°	186	17
15°	115	32
25°	68	31
35°	40	25
45°	24	19
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1266168

CATALOG NUMBER: P3AS02R159735DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	199.1
2.5°	195.8
5°	185.9
7.5°	170.1
10°	150.7
12.5°	131.6
15°	114.8
17.5°	100.7
20°	88.2
22.5°	77.3
25°	67.8
27.5°	59.2
30°	52.0
32.5°	45.7
35°	40.1
37.5°	35.2
40°	30.9
42.5°	27.3
45°	24.0
47.5°	21.4
50°	18.8
52.5°	16.5
55°	14.5
57.5°	12.8
60°	11.2
62.5°	9.5
65°	8.2
67.5°	6.9
70°	5.9
72.5°	4.6
75°	3.6
77.5°	2.6
80°	2.0
82.5°	1.0
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)