

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266169

Luminaire Tested: P3AS02R159735DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159735DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 106.0 lumens
Efficiency: N/A
Efficacy: 29.5 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266169
CATALOG NUMBER: P3AS02R159735DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1266169
 CATALOG NUMBER: P3AS02R159735DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.7	13.8
10°-20°	26.8	25.3
20°-30°	23.7	22.4
30°-40°	15.5	14.7
40°-50°	8.3	7.9
50°-60°	6.3	5.9
60°-70°	5.4	5.1
70°-80°	3.7	3.5
80°-90°	1.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	65.2	61.5
0°-40°	80.8	76.2
0°-60°	95.4	90.0
0°-90°	106.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	106.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	181	
5°	166	15
15°	96	27
25°	52	24
35°	25	16
45°	10	8
55°	7	6
65°	6	5
75°	4	4
85°	1	2
90°	0	



TEST NUMBER: P1266169
CATALOG NUMBER: P3AS02R159735DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	180.9
2.5°	176.7
5°	165.5
7.5°	149.1
10°	130.4
12.5°	112.3
15°	95.6
17.5°	82.1
20°	70.6
22.5°	60.4
25°	51.6
27.5°	43.7
30°	36.4
32.5°	30.2
35°	24.6
37.5°	19.7
40°	15.8
42.5°	12.5
45°	10.2
47.5°	8.9
50°	7.9
52.5°	7.6
55°	6.9
57.5°	6.6
60°	6.2
62.5°	5.9
65°	5.6
67.5°	4.9
70°	4.6
72.5°	3.9
75°	3.6
77.5°	3.0
80°	2.6
82.5°	2.3
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)