

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266181

Luminaire Tested: P3AS02R209735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 115.0 lumens
Efficiency: N/A
Efficacy: 32.0 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266181
CATALOG NUMBER: P3AS02R209735DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1266181

CATALOG NUMBER: P3AS02R209735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88480
5°	80431
10°	59451
15°	36777
20°	21002
25°	11976
30°	6735
35°	3667
40°	2004
45°	1116
50°	648
55°	459
60°	439
65°	415
70°	385
75°	339
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1116 cd/sqm



TEST NUMBER: P1266181
 CATALOG NUMBER: P3AS02R209735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.6	27.5
10°-20°	45.2	39.3
20°-30°	23.6	20.5
30°-40°	9.1	7.9
40°-50°	3.0	2.6
50°-60°	1.1	1.0
60°-70°	0.8	0.7
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	100.4	87.3
0°-40°	109.5	95.2
0°-60°	113.7	98.8
0°-90°	115.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	115.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	404	
5°	365	32
15°	162	45
25°	50	24
35°	14	9
45°	4	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1266181
CATALOG NUMBER: P3AS02R209735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	403.5
1°	402.7
2°	397.9
3°	390.6
4°	379.3
5°	365.4
6°	349.0
7°	330.7
8°	309.6
9°	289.1
10°	267.0
12.5°	212.2
15°	162.0
17.5°	121.2
20°	90.0
22.5°	66.7
25°	49.5
27.5°	36.6
30°	26.6
32.5°	19.2
35°	13.7
37.5°	9.9
40°	7.0
42.5°	5.0
45°	3.6
47.5°	2.6
50°	1.9
52.5°	1.4
55°	1.2
57.5°	1.1
60°	1.0
62.5°	0.9
65°	0.8
67.5°	0.7
70°	0.6
72.5°	0.6
75°	0.4
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)