

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266213

Luminaire Tested: P3AS02R259735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 89.0 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266213

CATALOG NUMBER: P3AS02R259735DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266213

CATALOG NUMBER: P3AS02R259735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		91
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		83
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		70
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		59
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		55
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		51
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21161
5°	20647
10°	19127
15°	17049
20°	14655
25°	12436
30°	10255
35°	7977
40°	5754
45°	3659
50°	2149
55°	1491
60°	1360
65°	1245
70°	1154
75°	1017
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3659 cd/sqm

TEST NUMBER: P1266213

CATALOG NUMBER: P3AS02R259735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.7	9.8
10°-20°	20.8	23.4
20°-30°	23.5	26.4
30°-40°	18.6	20.9
40°-50°	9.4	10.6
50°-60°	3.8	4.2
60°-70°	2.4	2.7
70°-80°	1.3	1.5
80°-90°	0.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	53.1	59.6
0°-40°	71.7	80.5
0°-60°	84.9	95.4
0°-90°	89.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	89.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	96	
5°	94	9
15°	75	21
25°	51	24
35°	30	19
45°	12	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1266213

CATALOG NUMBER: P3AS02R259735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	96.5
1°	96.5
2°	96.1
3°	95.6
4°	94.8
5°	93.8
6°	92.6
7°	91.1
8°	89.6
9°	87.8
10°	85.9
11°	83.8
12°	81.8
13°	79.5
14°	77.3
15°	75.1
17.5°	68.9
20°	62.8
22.5°	57.0
25°	51.4
27.5°	46.0
30°	40.5
32.5°	35.3
35°	29.8
37.5°	24.8
40°	20.1
42.5°	15.6
45°	11.8
47.5°	8.8
50°	6.3
52.5°	4.8
55°	3.9
57.5°	3.5
60°	3.1
62.5°	2.8
65°	2.4
67.5°	2.1
70°	1.8
72.5°	1.6
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.1



TEST NUMBER: P1266213

CATALOG NUMBER: P3AS02R259735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)