

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266223

Luminaire Tested: P3AS02R259735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266223
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 238.0 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266223
CATALOG NUMBER: P3AS02R259735DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1266223
 CATALOG NUMBER: P3AS02R259735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	85	82	79	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	82	78	76	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152663
5°	142439
10°	114093
15°	77458
20°	46857
25°	27413
30°	15597
35°	8593
40°	4551
45°	2388
50°	1399
55°	1032
60°	877
65°	934
70°	898
75°	763
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2388 cd/sqm



TEST NUMBER: P1266223
 CATALOG NUMBER: P3AS02R259735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.4	24.1
10°-20°	93.8	39.4
20°-30°	53.6	22.5
30°-40°	21.1	8.9
40°-50°	6.5	2.7
50°-60°	2.6	1.1
60°-70°	1.7	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	204.8	86.1
0°-40°	226.0	95.0
0°-60°	235.0	98.7
0°-90°	238.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	238.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	696	
5°	647	57
15°	341	94
25°	113	54
35°	32	21
45°	8	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266223
CATALOG NUMBER: P3AS02R259735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	696.2
1°	694.9
2°	689.2
3°	679.2
4°	665.3
5°	647.1
6°	625.7
7°	601.6
8°	573.6
9°	545.0
10°	512.4
11°	480.4
12°	445.1
13°	410.3
14°	374.6
15°	341.2
17.5°	264.5
20°	200.8
22.5°	150.8
25°	113.3
27.5°	83.9
30°	61.6
32.5°	44.6
35°	32.1
37.5°	22.7
40°	15.9
42.5°	10.9
45°	7.7
47.5°	5.5
50°	4.1
52.5°	3.2
55°	2.7
57.5°	2.5
60°	2.0
62.5°	1.8
65°	1.8
67.5°	1.6
70°	1.4
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.2



TEST NUMBER: P1266223
CATALOG NUMBER: P3AS02R259735DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)