

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267027

Luminaire Tested: P3AS09R309735DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309735DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 861.0 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267027

CATALOG NUMBER: P3AS09R309735DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267027

CATALOG NUMBER: P3AS09R309735DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	87	86
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	685033
5°	676093
10°	590303
15°	375212
20°	148646
25°	49648
30°	23092
35°	10467
40°	4008
45°	1985
50°	580
55°	268
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1985 cd/sqm

TEST NUMBER: P1267027

CATALOG NUMBER: P3AS09R309735DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	280.8	32.6
10°-20°	435.5	50.6
20°-30°	112.3	13.0
30°-40°	26.4	3.1
40°-50°	5.2	0.6
50°-60°	0.6	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	828.6	96.2
0°-40°	855.0	99.3
0°-60°	860.7	100.0
0°-90°	861.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	861.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3124	
5°	3072	281
15°	1653	435
25°	205	112
35°	39	26
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267027

CATALOG NUMBER: P3AS09R309735DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3124.0
1°	3121.7
2°	3114.3
3°	3106.0
4°	3093.6
5°	3071.5
6°	3035.8
7°	2976.3
8°	2895.1
9°	2789.1
10°	2651.1
11°	2487.0
12°	2307.8
13°	2101.6
14°	1885.7
15°	1652.8
16°	1424.5
17°	1204.6
18°	993.7
19°	800.1
20°	637.0
21°	501.3
22°	394.4
23°	312.2
24°	250.0
25°	205.2
26°	171.1
27°	145.4
28°	125.7
29°	107.6
30°	91.2
32.5°	57.5
35°	39.1
37.5°	24.4
40°	14.0
42.5°	9.4
45°	6.4
47.5°	3.7
50°	1.7
52.5°	0.7
55°	0.7
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3



TEST NUMBER: P1267027

CATALOG NUMBER: P3AS09R309735DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)