

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267099

Luminaire Tested: P3AS09R409735DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409735DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 609.0 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267099

CATALOG NUMBER: P3AS09R409735DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267099

CATALOG NUMBER: P3AS09R409735DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136700
5°	134228
10°	126517
15°	114916
20°	100972
25°	86207
30°	71429
35°	55091
40°	39216
45°	26421
50°	14396
55°	10169
60°	9561
65°	8821
70°	7886
75°	7540
80°	6061
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26421 cd/sqm

TEST NUMBER: P1267099

CATALOG NUMBER: P3AS09R409735DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	9.3
10°-20°	141.0	23.2
20°-30°	163.0	26.8
30°-40°	128.5	21.1
40°-50°	66.0	10.8
50°-60°	25.2	4.1
60°-70°	16.7	2.7
70°-80°	9.1	1.5
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.9	59.3
0°-40°	489.4	80.4
0°-60°	580.6	95.3
0°-90°	609.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	609.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	623	
5°	610	57
15°	506	141
25°	356	163
35°	206	128
45°	85	66
55°	27	25
65°	17	17
75°	9	9
85°	2	3
90°	0	

TEST NUMBER: P1267099

CATALOG NUMBER: P3AS09R409735DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	623.4
2.5°	620.0
5°	609.8
7.5°	592.1
10°	568.2
12.5°	540.3
15°	506.2
17.5°	470.8
20°	432.7
22.5°	393.8
25°	356.3
27.5°	318.9
30°	282.1
32.5°	244.6
35°	205.8
37.5°	169.7
40°	137.0
42.5°	109.0
45°	85.2
47.5°	62.0
50°	42.2
52.5°	30.7
55°	26.6
57.5°	23.8
60°	21.8
62.5°	19.1
65°	17.0
67.5°	14.3
70°	12.3
72.5°	10.2
75°	8.9
77.5°	6.8
80°	4.8
82.5°	4.1
85°	2.0
87.5°	1.4
90°	0.0

(END OF REPORT)