

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267104

Luminaire Tested: P3AS09R409735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 794.0 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267104
CATALOG NUMBER: P3AS09R409735DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1267104
 CATALOG NUMBER: P3AS09R409735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	351332
5°	341139
10°	309569
15°	255734
20°	184489
25°	114103
30°	61782
35°	31936
40°	17375
45°	9706
50°	4878
55°	3632
60°	3289
65°	3165
70°	3077
75°	2881
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9706 cd/sqm



TEST NUMBER: P1267104
 CATALOG NUMBER: P3AS09R409735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.9	18.0
10°-20°	306.8	38.6
20°-30°	218.9	27.6
30°-40°	80.6	10.2
40°-50°	25.4	3.2
50°-60°	8.8	1.1
60°-70°	6.1	0.8
70°-80°	3.6	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	668.5	84.2
0°-40°	749.1	94.3
0°-60°	783.3	98.7
0°-90°	794.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	794.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1602	
5°	1550	143
15°	1126	307
25°	472	219
35°	119	81
45°	31	25
55°	10	9
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1267104
CATALOG NUMBER: P3AS09R409735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1602.2
2.5°	1590.0
5°	1549.8
7.5°	1483.0
10°	1390.3
12.5°	1272.4
15°	1126.5
17.5°	963.0
20°	790.6
22.5°	620.9
25°	471.6
27.5°	346.2
30°	244.0
32.5°	171.1
35°	119.3
37.5°	84.5
40°	60.7
42.5°	43.6
45°	31.3
47.5°	21.1
50°	14.3
52.5°	10.2
55°	9.5
57.5°	8.9
60°	7.5
62.5°	6.8
65°	6.1
67.5°	5.5
70°	4.8
72.5°	4.1
75°	3.4
77.5°	2.7
80°	2.0
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)