

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267119

Luminaire Tested: P3AS09R459735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 290.0 lumens
Efficiency: N/A
Efficacy: 26.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267119
CATALOG NUMBER: P3AS09R459735DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1267119
 CATALOG NUMBER: P3AS09R459735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61486
5°	60400
10°	57158
15°	52123
20°	46087
25°	40018
30°	34360
35°	28616
40°	21326
45°	13056
50°	6038
55°	4741
60°	4561
65°	4151
70°	3847
75°	3643
80°	3410
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13056 cd/sqm



TEST NUMBER: P1267119
 CATALOG NUMBER: P3AS09R459735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.6	8.8
10°-20°	63.9	22.0
20°-30°	75.9	26.2
30°-40°	66.0	22.8
40°-50°	33.1	11.4
50°-60°	11.5	4.0
60°-70°	8.1	2.8
70°-80°	4.5	1.5
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.5	57.1
0°-40°	231.5	79.8
0°-60°	276.1	95.2
0°-90°	290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	290.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	280	
5°	274	26
15°	230	64
25°	165	76
35°	107	66
45°	42	33
55°	12	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1267119
CATALOG NUMBER: P3AS09R459735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	280.4
2.5°	279.1
5°	274.4
7.5°	267.0
10°	256.7
12.5°	244.0
15°	229.6
17.5°	213.6
20°	197.5
22.5°	181.1
25°	165.4
27.5°	150.4
30°	135.7
32.5°	121.7
35°	106.9
37.5°	91.2
40°	74.5
42.5°	58.2
45°	42.1
47.5°	27.7
50°	17.7
52.5°	13.7
55°	12.4
57.5°	11.4
60°	10.4
62.5°	9.4
65°	8.0
67.5°	7.0
70°	6.0
72.5°	5.0
75°	4.3
77.5°	3.3
80°	2.7
82.5°	2.0
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)