

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266284

Luminaire Tested: P3AS02R359735DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359735DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 147.0 lumens
Efficiency: N/A
Efficacy: 40.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266284

CATALOG NUMBER: P3AS02R359735DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266284

CATALOG NUMBER: P3AS02R359735DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		83	80	77		82
5	92	83	77	73	90	82	77	73	80	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47255
5°	46093
10°	42128
15°	35755
20°	28306
25°	21413
30°	15597
35°	10547
40°	6469
45°	3721
50°	2252
55°	1835
60°	1579
65°	1401
70°	1154
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3721 cd/sqm

TEST NUMBER: P1266284

CATALOG NUMBER: P3AS02R359735DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.3	13.2
10°-20°	43.4	29.5
20°-30°	40.6	27.6
30°-40°	24.9	16.9
40°-50°	9.8	6.7
50°-60°	4.3	2.9
60°-70°	2.7	1.8
70°-80°	1.4	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	103.4	70.3
0°-40°	128.3	87.2
0°-60°	142.4	96.8
0°-90°	147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	147.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	216	
5°	209	19
15°	158	43
25°	88	41
35°	39	25
45°	12	10
55°	5	4
65°	3	3
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P1266284

CATALOG NUMBER: P3AS02R359735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	215.5
1°	215.7
2°	215.0
3°	213.7
4°	211.6
5°	209.4
6°	206.4
7°	203.0
8°	199.0
9°	194.4
10°	189.2
11°	183.8
12°	177.9
13°	171.6
14°	164.5
15°	157.5
17.5°	139.4
20°	121.3
22.5°	103.9
25°	88.5
27.5°	74.2
30°	61.6
32.5°	49.8
35°	39.4
37.5°	30.1
40°	22.6
42.5°	16.3
45°	12.0
47.5°	8.6
50°	6.6
52.5°	5.4
55°	4.8
57.5°	4.1
60°	3.6
62.5°	3.2
65°	2.7
67.5°	2.3
70°	1.8
72.5°	1.6
75°	1.4
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2



TEST NUMBER: P1266284

CATALOG NUMBER: P3AS02R359735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)