

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266299

Luminaire Tested: P3AS02R409735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266299
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 130.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266299

CATALOG NUMBER: P3AS02R409735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1266299

CATALOG NUMBER: P3AS02R409735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		94
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		89
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		84
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		80
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		76
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		72
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		69
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		65
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		63
10	78	70	65	62	78	70	65	62	69	64	61		68	64	61		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57517
5°	55844
10°	50678
15°	41862
20°	30196
25°	18678
30°	10103
35°	5220
40°	2834
45°	1582
50°	785
55°	612
60°	526
65°	519
70°	513
75°	508
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1582 cd/sqm

TEST NUMBER: P1266299

CATALOG NUMBER: P3AS02R409735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.4	18.0
10°-20°	50.2	38.6
20°-30°	35.8	27.6
30°-40°	13.2	10.1
40°-50°	4.1	3.2
50°-60°	1.5	1.1
60°-70°	1.0	0.8
70°-80°	0.6	0.5
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.5	84.2
0°-40°	122.6	94.4
0°-60°	128.2	98.7
0°-90°	130.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	130.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	262	
5°	254	23
15°	184	50
25°	77	36
35°	20	13
45°	5	4
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266299

CATALOG NUMBER: P3AS02R409735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	262.3
2.5°	260.3
5°	253.7
7.5°	242.8
10°	227.6
12.5°	208.3
15°	184.4
17.5°	157.7
20°	129.4
22.5°	101.7
25°	77.2
27.5°	56.7
30°	39.9
32.5°	28.0
35°	19.5
37.5°	13.8
40°	9.9
42.5°	7.1
45°	5.1
47.5°	3.5
50°	2.3
52.5°	1.7
55°	1.6
57.5°	1.5
60°	1.2
62.5°	1.1
65°	1.0
67.5°	0.9
70°	0.8
72.5°	0.7
75°	0.6
77.5°	0.4
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)