

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267120

Luminaire Tested: P3AS09R459735DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459735DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 592.0 lumens
Efficiency: N/A
Efficacy: 53.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267120

CATALOG NUMBER: P3AS09R459735DE010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1267120

CATALOG NUMBER: P3AS09R459735DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125516
5°	123288
10°	116676
15°	106402
20°	94088
25°	81706
30°	70137
35°	58437
40°	43539
45°	26669
50°	12349
55°	9634
60°	9254
65°	8509
70°	7886
75°	7540
80°	6945
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26669 cd/sqm

TEST NUMBER: P1267120

CATALOG NUMBER: P3AS09R459735DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	8.8
10°-20°	130.5	22.0
20°-30°	155.0	26.2
30°-40°	134.7	22.8
40°-50°	67.6	11.4
50°-60°	23.5	4.0
60°-70°	16.4	2.8
70°-80°	9.2	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.9	57.1
0°-40°	472.6	79.8
0°-60°	563.6	95.2
0°-90°	592.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	592.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	572	
5°	560	52
15°	469	130
25°	338	155
35°	218	135
45°	86	68
55°	25	23
65°	16	16
75°	9	9
85°	2	3
90°	0	

TEST NUMBER: P1267120

CATALOG NUMBER: P3AS09R459735DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	572.4
2.5°	569.7
5°	560.1
7.5°	545.1
10°	524.0
12.5°	498.0
15°	468.7
17.5°	436.0
20°	403.2
22.5°	369.8
25°	337.7
27.5°	307.0
30°	277.0
32.5°	248.3
35°	218.3
37.5°	186.3
40°	152.1
42.5°	118.7
45°	86.0
47.5°	56.6
50°	36.2
52.5°	28.0
55°	25.2
57.5°	23.2
60°	21.1
62.5°	19.1
65°	16.4
67.5°	14.3
70°	12.3
72.5°	10.2
75°	8.9
77.5°	6.8
80°	5.5
82.5°	4.1
85°	2.0
87.5°	1.4
90°	0.0

(END OF REPORT)