

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267159

Luminaire Tested: P3AS09R509735DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267159  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R509735DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 503.0 lumens  
Efficiency: N/A  
Efficacy: 45.3 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267159  
CATALOG NUMBER: P3AS09R509735DE010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1267159  
 CATALOG NUMBER: P3AS09R509735DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	146304
5°	142351
10°	131282
15°	115438
20°	96585
25°	76601
30°	56186
35°	38628
40°	24560
45°	13738
50°	7437
55°	6232
60°	5394
65°	4929
70°	4360
75°	4067
80°	3410
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13738 cd/sqm



TEST NUMBER: P1267159  
 CATALOG NUMBER: P3AS09R509735DE010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.9	11.9
10°-20°	140.8	28.0
20°-30°	144.1	28.6
30°-40°	91.3	18.2
40°-50°	36.4	7.2
50°-60°	14.7	2.9
60°-70°	9.4	1.9
70°-80°	4.8	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	344.8	68.5
0°-40°	436.1	86.7
0°-60°	487.3	96.9
0°-90°	503.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	503.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	667	
5°	647	60
15°	508	141
25°	317	144
35°	144	91
45°	44	36
55°	16	15
65°	10	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1267159  
CATALOG NUMBER: P3AS09R509735DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	667.2
2.5°	662.4
5°	646.7
7.5°	622.2
10°	589.6
12.5°	550.7
15°	508.5
17.5°	462.2
20°	413.9
22.5°	365.6
25°	316.6
27.5°	267.5
30°	221.9
32.5°	181.1
35°	144.3
37.5°	113.0
40°	85.8
42.5°	63.3
45°	44.3
47.5°	30.0
50°	21.8
52.5°	18.4
55°	16.3
57.5°	14.3
60°	12.3
62.5°	10.9
65°	9.5
67.5°	8.2
70°	6.8
72.5°	5.4
75°	4.8
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)