

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266359

Luminaire Tested: P3AS02R509735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 97.0 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266359
CATALOG NUMBER: P3AS02R509735DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1266359
 CATALOG NUMBER: P3AS02R509735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19713
5°	19414
10°	18570
15°	17185
20°	15448
25°	13573
30°	11546
35°	9369
40°	7042
45°	4528
50°	2149
55°	1682
60°	1623
65°	1505
70°	1346
75°	1186
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4528 cd/sqm



TEST NUMBER: P1266359
 CATALOG NUMBER: P3AS02R509735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.3	8.5
10°-20°	21.1	21.8
20°-30°	25.6	26.4
30°-40°	21.8	22.4
40°-50°	11.3	11.6
50°-60°	4.1	4.2
60°-70°	2.8	2.9
70°-80°	1.5	1.6
80°-90°	0.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	55.0	56.7
0°-40°	76.8	79.2
0°-60°	92.2	95.0
0°-90°	97.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	97.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	90	
5°	88	8
15°	76	21
25°	56	26
35°	35	22
45°	15	11
55°	4	4
65°	3	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P1266359
CATALOG NUMBER: P3AS02R509735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	89.9
2.5°	89.6
5°	88.2
7.5°	86.2
10°	83.4
12.5°	79.7
15°	75.7
17.5°	71.2
20°	66.2
22.5°	61.1
25°	56.1
27.5°	50.9
30°	45.6
32.5°	40.3
35°	35.0
37.5°	29.8
40°	24.6
42.5°	19.6
45°	14.6
47.5°	9.7
50°	6.3
52.5°	4.9
55°	4.4
57.5°	4.0
60°	3.7
62.5°	3.2
65°	2.9
67.5°	2.4
70°	2.1
72.5°	1.8
75°	1.4
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)