

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266457

Luminaire Tested: P3AS02R659735DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266457
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659735DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 157.0 lumens
Efficiency: N/A
Efficacy: 43.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266457

CATALOG NUMBER: P3AS02R659735DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266457

CATALOG NUMBER: P3AS02R659735DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39909
5°	38917
10°	36227
15°	32486
20°	28049
25°	23324
30°	18408
35°	13626
40°	9389
45°	5830
50°	3173
55°	1988
60°	1667
65°	1505
70°	1282
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5830 cd/sqm

TEST NUMBER: P1266457

CATALOG NUMBER: P3AS02R659735DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.4	10.5
10°-20°	39.8	25.3
20°-30°	44.0	28.0
30°-40°	31.9	20.3
40°-50°	15.0	9.5
50°-60°	5.0	3.2
60°-70°	2.9	1.8
70°-80°	1.5	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	100.1	63.8
0°-40°	132.1	84.1
0°-60°	152.0	96.9
0°-90°	157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	182	
5°	177	16
15°	143	40
25°	96	44
35°	51	32
45°	19	15
55°	5	5
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P1266457

CATALOG NUMBER: P3AS02R659735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	182.0
2.5°	180.9
5°	176.8
7.5°	170.7
10°	162.7
12.5°	153.5
15°	143.1
17.5°	131.7
20°	120.2
22.5°	108.2
25°	96.4
27.5°	84.4
30°	72.7
32.5°	61.3
35°	50.9
37.5°	41.4
40°	32.8
42.5°	25.1
45°	18.8
47.5°	13.6
50°	9.3
52.5°	6.3
55°	5.2
57.5°	4.5
60°	3.8
62.5°	3.4
65°	2.9
67.5°	2.5
70°	2.0
72.5°	1.8
75°	1.4
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)