

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267229

Luminaire Tested: P3AS09R659735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267229
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 335.0 lumens
Efficiency: N/A
Efficacy: 30.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267229

CATALOG NUMBER: P3AS09R659735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267229

CATALOG NUMBER: P3AS09R659735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79007
5°	78054
10°	75082
15°	70352
20°	63262
25°	53713
30°	42006
35°	29955
40°	19608
45°	12125
50°	6141
55°	2179
60°	1886
65°	1920
70°	1731
75°	1694
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12125 cd/sqm

TEST NUMBER: P1267229

CATALOG NUMBER: P3AS09R659735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.3	9.9
10°-20°	86.2	25.7
20°-30°	100.8	30.1
30°-40°	70.4	21.0
40°-50°	31.0	9.3
50°-60°	6.9	2.1
60°-70°	3.5	1.0
70°-80°	2.1	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.3	65.8
0°-40°	290.7	86.8
0°-60°	328.6	98.1
0°-90°	335.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	335.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	360	
5°	355	33
15°	310	86
25°	222	101
35°	112	70
45°	39	31
55°	6	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1267229

CATALOG NUMBER: P3AS09R659735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	360.3
2.5°	358.9
5°	354.6
7.5°	347.3
10°	337.2
12.5°	324.9
15°	309.9
17.5°	291.5
20°	271.1
22.5°	248.1
25°	222.0
27.5°	194.7
30°	165.9
32.5°	138.2
35°	111.9
37.5°	88.8
40°	68.5
42.5°	51.8
45°	39.1
47.5°	28.7
50°	18.0
52.5°	9.3
55°	5.7
57.5°	5.0
60°	4.3
62.5°	4.0
65°	3.7
67.5°	3.0
70°	2.7
72.5°	2.3
75°	2.0
77.5°	1.7
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)