

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267254

Luminaire Tested: P3AS09R709735DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709735DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 813.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267254
CATALOG NUMBER: P3AS09R709735DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1267254

CATALOG NUMBER: P3AS09R709735DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57	57	57	57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158079
5°	149064
10°	141347
15°	138798
20°	133782
25°	126104
30°	125209
35°	109058
40°	70532
45°	33337
50°	4674
55°	382
60°	307
65°	363
70°	192
75°	254
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33337 cd/sqm



TEST NUMBER: P1267254

CATALOG NUMBER: P3AS09R709735DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	7.8
10°-20°	171.7	21.1
20°-30°	242.9	29.9
30°-40°	244.1	30.0
40°-50°	87.8	10.8
50°-60°	2.4	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.8	58.8
0°-40°	721.9	88.8
0°-60°	812.1	99.9
0°-90°	813.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	813.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	721	
5°	677	63
15°	611	172
25°	521	243
35°	407	244
45°	108	88
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1267254

CATALOG NUMBER: P3AS09R709735DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	720.9
1°	718.9
2°	712.6
3°	702.5
4°	689.9
5°	677.2
6°	665.2
7°	655.8
8°	647.5
9°	640.8
10°	634.8
11°	629.8
12°	625.1
13°	620.4
14°	616.1
15°	611.4
16°	605.7
17°	599.7
18°	592.4
19°	583.3
20°	573.3
21°	562.3
22°	551.3
23°	540.6
24°	530.3
25°	521.2
26°	514.9
27°	509.9
28°	505.9
29°	501.2
30°	494.5
31°	484.8
32°	471.1
32.5°	463.5
33°	453.1
34°	432.7
35°	407.4
36°	379.3
37°	347.6
37.5°	332.9
38°	312.9
39°	277.1
40°	246.4
42.5°	170.6
45°	107.5



TEST NUMBER: P1267254
CATALOG NUMBER: P3AS09R709735DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	57.8
50°	13.7
52.5°	1.7
55°	1.0
57.5°	1.0
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)