

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266547

Luminaire Tested: P3AS05R129735DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129735DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 349.9 lumens
Efficiency: N/A
Efficacy: 46.0 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266547

CATALOG NUMBER: P3AS05R129735DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266547

CATALOG NUMBER: P3AS05R129735DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90		
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80		
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72		
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60		
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55		
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101856
5°	95487
10°	78288
15°	60818
20°	48024
25°	38276
30°	30714
35°	25083
40°	20667
45°	17366
50°	14942
55°	12922
60°	11446
65°	9962
70°	8848
75°	7117
80°	5809
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17366 cd/sqm

TEST NUMBER: P1266547

CATALOG NUMBER: P3AS05R129735DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	11.1
10°-20°	75.0	21.4
20°-30°	73.0	20.8
30°-40°	59.0	16.8
40°-50°	43.8	12.5
50°-60°	30.6	8.7
60°-70°	19.2	5.5
70°-80°	9.1	2.6
80°-90°	1.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.7	53.4
0°-40°	245.7	70.2
0°-60°	320.1	91.5
0°-90°	349.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	349.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	464	
5°	434	39
15°	268	75
25°	158	73
35°	94	59
45°	56	44
55°	34	31
65°	19	19
75°	8	9
85°	2	2
90°	0	

TEST NUMBER: P1266547

CATALOG NUMBER: P3AS05R129735DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	464.5
2.5°	456.8
5°	433.8
7.5°	396.9
10°	351.6
12.5°	307.1
15°	267.9
17.5°	234.9
20°	205.8
22.5°	180.4
25°	158.2
27.5°	138.2
30°	121.3
32.5°	106.7
35°	93.7
37.5°	82.1
40°	72.2
42.5°	63.7
45°	56.0
47.5°	49.9
50°	43.8
52.5°	38.4
55°	33.8
57.5°	29.9
60°	26.1
62.5°	22.3
65°	19.2
67.5°	16.1
70°	13.8
72.5°	10.7
75°	8.4
77.5°	6.1
80°	4.6
82.5°	2.3
85°	1.5
87.5°	0.0
90°	0.0

(END OF REPORT)