

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266576

Luminaire Tested: P3AS05R159735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 484.0 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266576

CATALOG NUMBER: P3AS05R159735DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1266576

CATALOG NUMBER: P3AS05R159735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	413454
5°	367003
10°	254883
15°	150716
20°	85851
25°	49067
30°	27143
35°	14482
40°	8015
45°	4342
50°	2695
55°	2141
60°	1842
65°	1712
70°	1475
75°	1610
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4342 cd/sqm

TEST NUMBER: P1266576

CATALOG NUMBER: P3AS05R159735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.8	29.3
10°-20°	187.1	38.7
20°-30°	96.3	19.9
30°-40°	36.2	7.5
40°-50°	11.8	2.4
50°-60°	5.1	1.1
60°-70°	3.2	0.7
70°-80°	1.9	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.2	87.9
0°-40°	461.4	95.3
0°-60°	478.4	98.8
0°-90°	484.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	484.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1886	
5°	1667	142
15°	664	187
25°	203	96
35°	54	36
45°	14	12
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1266576

CATALOG NUMBER: P3AS05R159735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1885.5
1°	1881.8
2°	1857.1
3°	1810.0
4°	1748.0
5°	1667.3
6°	1575.9
7°	1475.7
8°	1364.3
9°	1254.2
10°	1144.7
12.5°	880.8
15°	663.9
17.5°	497.0
20°	367.9
22.5°	274.6
25°	202.8
27.5°	147.8
30°	107.2
32.5°	76.0
35°	54.1
37.5°	38.7
40°	28.0
42.5°	20.0
45°	14.0
47.5°	10.3
50°	7.9
52.5°	6.5
55°	5.6
57.5°	4.7
60°	4.2
62.5°	3.7
65°	3.3
67.5°	2.8
70°	2.3
72.5°	2.3
75°	1.9
77.5°	1.4
80°	0.9
82.5°	0.9
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)