

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267329

Luminaire Tested: P3AS13R129735DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267329
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129735DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 97CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 649.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267329
CATALOG NUMBER: P3AS13R129735DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1267329
 CATALOG NUMBER: P3AS13R129735DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163693
5°	159256
10°	145533
15°	127470
20°	109350
25°	91312
30°	73075
35°	54797
40°	39760
45°	26018
50°	16272
55°	11010
60°	9736
65°	8976
70°	8463
75°	7625
80°	7324
85°	6290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26018 cd/sqm



TEST NUMBER: P1267329
 CATALOG NUMBER: P3AS13R129735DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.8	10.3
10°-20°	156.5	24.1
20°-30°	172.4	26.6
30°-40°	129.1	19.9
40°-50°	66.9	10.3
50°-60°	27.8	4.3
60°-70°	17.2	2.6
70°-80°	9.7	1.5
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	395.6	61.0
0°-40°	524.7	80.8
0°-60°	619.4	95.4
0°-90°	649.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	649.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	746	
5°	724	67
15°	562	156
25°	377	172
35°	205	129
45°	84	67
55°	29	28
65°	17	17
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P1267329
CATALOG NUMBER: P3AS13R129735DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	746.5
1°	747.4
2°	744.9
3°	740.0
4°	732.6
5°	723.5
6°	712.0
7°	699.7
8°	684.9
9°	669.3
10°	653.6
12.5°	608.4
15°	561.5
17.5°	514.7
20°	468.6
22.5°	421.8
25°	377.4
27.5°	333.0
30°	288.6
32.5°	245.0
35°	204.7
37.5°	170.2
40°	138.9
42.5°	110.2
45°	83.9
47.5°	63.3
50°	47.7
52.5°	35.4
55°	28.8
57.5°	25.5
60°	22.2
62.5°	19.7
65°	17.3
67.5°	14.8
70°	13.2
72.5°	10.7
75°	9.0
77.5°	7.4
80°	5.8
82.5°	4.1
85°	2.5
87.5°	0.8
90°	0.0

(END OF REPORT)