

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266592

Luminaire Tested: P3AS05R209735DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1266592  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R209735DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 237.0 lumens  
Efficiency: N/A  
Efficacy: 32.9 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1266592  
CATALOG NUMBER: P3AS05R209735DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1266592

CATALOG NUMBER: P3AS05R209735DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 95  | 95  | 95  | 95  |
| 2   | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98  | 101 | 98  | 96  | 98  | 96  | 94  | 95  | 94  | 92  | 91  | 91  | 91  | 91  |
| 3   | 106 | 100 | 96  | 93  | 104 | 99  | 95  | 92  | 97  | 93  | 91  | 94  | 92  | 89  | 92  | 90  | 88  | 87  | 87  | 87  | 87  |
| 4   | 102 | 96  | 91  | 88  | 100 | 95  | 90  | 87  | 92  | 89  | 86  | 91  | 88  | 85  | 89  | 86  | 84  | 83  | 83  | 83  | 83  |
| 5   | 98  | 91  | 87  | 83  | 97  | 90  | 86  | 83  | 89  | 85  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 79  | 79  | 79  | 79  |
| 6   | 95  | 87  | 83  | 79  | 93  | 87  | 82  | 79  | 85  | 81  | 78  | 84  | 81  | 78  | 83  | 80  | 77  | 76  | 76  | 76  | 76  |
| 7   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 75  | 81  | 78  | 75  | 80  | 77  | 75  | 73  | 73  | 73  | 73  |
| 8   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 79  | 75  | 72  | 78  | 75  | 72  | 78  | 74  | 72  | 71  | 71  | 71  | 71  |
| 9   | 85  | 78  | 73  | 70  | 85  | 77  | 73  | 70  | 77  | 73  | 70  | 76  | 72  | 69  | 75  | 72  | 69  | 68  | 68  | 68  | 68  |
| 10  | 83  | 75  | 71  | 68  | 82  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 70  | 67  | 73  | 69  | 67  | 66  | 66  | 66  | 66  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 182354 |
| 5°  | 165749 |
| 10° | 122509 |
| 15° | 75778  |
| 20° | 43287  |
| 25° | 24703  |
| 30° | 13850  |
| 35° | 7549   |
| 40° | 4122   |
| 45° | 2264   |
| 50° | 1330   |
| 55° | 956    |
| 60° | 921    |
| 65° | 830    |
| 70° | 705    |
| 75° | 763    |
| 80° | 631    |
| 85° | 503    |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2264 cd/sqm



TEST NUMBER: P1266592  
 CATALOG NUMBER: P3AS05R209735DE010 E3DL1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 65.2   | 27.5      |
| 10°-20°   | 93.1   | 39.3      |
| 20°-30°   | 48.6   | 20.5      |
| 30°-40°   | 18.8   | 7.9       |
| 40°-50°   | 6.1    | 2.6       |
| 50°-60°   | 2.4    | 1.0       |
| 60°-70°   | 1.6    | 0.7       |
| 70°-80°   | 0.9    | 0.4       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 206.9  | 87.3      |
| 0°-40°    | 225.7  | 95.2      |
| 0°-60°    | 234.2  | 98.8      |
| 0°-90°    | 237.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 237.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 832 |      |
| 5°  | 753 | 65   |
| 15° | 334 | 93   |
| 25° | 102 | 49   |
| 35° | 28  | 19   |
| 45° | 7   | 6    |
| 55° | 2   | 2    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P1266592  
CATALOG NUMBER: P3AS05R209735DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 831.6 |
| 1°    | 830.0 |
| 2°    | 820.1 |
| 3°    | 805.0 |
| 4°    | 781.6 |
| 5°    | 753.0 |
| 6°    | 719.1 |
| 7°    | 681.6 |
| 8°    | 638.1 |
| 9°    | 595.7 |
| 10°   | 550.2 |
| 12.5° | 437.3 |
| 15°   | 333.8 |
| 17.5° | 249.8 |
| 20°   | 185.5 |
| 22.5° | 137.4 |
| 25°   | 102.1 |
| 27.5° | 75.3  |
| 30°   | 54.7  |
| 32.5° | 39.6  |
| 35°   | 28.2  |
| 37.5° | 20.4  |
| 40°   | 14.4  |
| 42.5° | 10.3  |
| 45°   | 7.3   |
| 47.5° | 5.3   |
| 50°   | 3.9   |
| 52.5° | 3.0   |
| 55°   | 2.5   |
| 57.5° | 2.3   |
| 60°   | 2.1   |
| 62.5° | 1.8   |
| 65°   | 1.6   |
| 67.5° | 1.4   |
| 70°   | 1.1   |
| 72.5° | 1.1   |
| 75°   | 0.9   |
| 77.5° | 0.7   |
| 80°   | 0.5   |
| 82.5° | 0.5   |
| 85°   | 0.2   |
| 87.5° | 0.2   |
| 90°   | 0.0   |

(END OF REPORT)