

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266619

Luminaire Tested: P3AS05R259735DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259735DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 488.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266619
CATALOG NUMBER: P3AS05R259735DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1266619
 CATALOG NUMBER: P3AS05R259735DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	90
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	86
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	91	89	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	88	85	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	313023
5°	292053
10°	233952
15°	158798
20°	96095
25°	56205
30°	32005
35°	17614
40°	9332
45°	4931
50°	2866
55°	2141
60°	1842
65°	1920
70°	1795
75°	1610
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4931 cd/sqm



TEST NUMBER: P1266619
 CATALOG NUMBER: P3AS05R259735DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.7	24.1
10°-20°	192.3	39.4
20°-30°	109.9	22.5
30°-40°	43.4	8.9
40°-50°	13.3	2.7
50°-60°	5.2	1.1
60°-70°	3.5	0.7
70°-80°	2.0	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.0	86.1
0°-40°	463.3	94.9
0°-60°	481.9	98.7
0°-90°	488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1428	
5°	1327	118
15°	700	192
25°	232	110
35°	66	43
45°	16	13
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1266619
CATALOG NUMBER: P3AS05R259735DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1427.5
1°	1424.7
2°	1413.1
3°	1392.6
4°	1364.1
5°	1326.8
6°	1283.0
7°	1233.5
8°	1176.2
9°	1117.4
10°	1050.7
11°	985.0
12°	912.7
13°	841.3
14°	768.1
15°	699.5
17.5°	542.4
20°	411.8
22.5°	309.2
25°	232.3
27.5°	172.1
30°	126.4
32.5°	91.4
35°	65.8
37.5°	46.6
40°	32.6
42.5°	22.4
45°	15.9
47.5°	11.2
50°	8.4
52.5°	6.5
55°	5.6
57.5°	5.1
60°	4.2
62.5°	3.7
65°	3.7
67.5°	3.3
70°	2.8
72.5°	2.3
75°	1.9
77.5°	1.4
80°	0.9
82.5°	0.9
85°	0.5
87.5°	0.5



TEST NUMBER: P1266619
CATALOG NUMBER: P3AS05R259735DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)