

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267372

Luminaire Tested: P3AS13R209735DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209735DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1144.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267372

CATALOG NUMBER: P3AS13R209735DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1267372

CATALOG NUMBER: P3AS13R209735DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105		104	103	102		101	100	99	98
2	112	109	107	104	110	108	105	103	104	103	101		102	100	99		99	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97		99	98	96		97	96	95	93
4	107	102	99	96	105	101	98	96	99	97	95		97	95	93		96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92		95	93	91		94	92	91	90
6	102	97	93	91	101	96	93	90	95	92	90		94	91	89		93	90	89	88
7	100	94	91	88	99	94	91	88	93	90	88		92	89	87		91	89	87	86
8	98	92	89	86	97	92	89	86	91	88	86		90	88	86		89	87	85	85
9	96	90	87	85	95	90	87	85	89	86	84		89	86	84		88	86	84	83
10	94	89	85	83	93	88	85	83	88	85	83		87	84	83		87	84	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1776766
5°	1542171
10°	952888
15°	330967
20°	101649
25°	35929
30°	13293
35°	5327
40°	2863
45°	1116
50°	614
55°	688
60°	789
65°	467
70°	577
75°	763
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1116 cd/sqm

TEST NUMBER: P1267372

CATALOG NUMBER: P3AS13R209735DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	581.5	50.8
10°-20°	461.4	40.3
20°-30°	79.9	7.0
30°-40°	14.5	1.3
40°-50°	3.3	0.3
50°-60°	1.6	0.1
60°-70°	1.0	0.1
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1122.7	98.1
0°-40°	1137.2	99.4
0°-60°	1142.1	99.8
0°-90°	1144.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1144.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8103	
5°	7006	581
15°	1458	461
25°	148	80
35°	20	15
45°	4	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1267372

CATALOG NUMBER: P3AS13R209735DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8102.7
1°	8063.7
2°	7909.8
3°	7662.6
4°	7372.8
5°	7006.1
6°	6585.9
7°	6096.9
8°	5540.0
9°	4914.3
10°	4279.5
12.5°	2699.4
15°	1457.9
17.5°	778.8
20°	435.6
22.5°	249.0
25°	148.5
27.5°	90.6
30°	52.5
32.5°	30.8
35°	19.9
37.5°	13.6
40°	10.0
42.5°	6.3
45°	3.6
47.5°	1.8
50°	1.8
52.5°	1.8
55°	1.8
57.5°	1.8
60°	1.8
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)