

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267376

Luminaire Tested: P3AS13R209735DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209735DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1135.0 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267376

CATALOG NUMBER: P3AS13R209735DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1267376

CATALOG NUMBER: P3AS13R209735DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89	89	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	87	87	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83	83	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	81	81	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1721704
5°	1449589
10°	905416
15°	338504
20°	116187
25°	48414
30°	22814
35°	10226
40°	4838
45°	2481
50°	921
55°	153
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2481 cd/sqm

TEST NUMBER: P1267376

CATALOG NUMBER: P3AS13R209735DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	547.6	48.3
10°-20°	451.1	39.7
20°-30°	102.5	9.0
30°-40°	26.1	2.3
40°-50°	6.6	0.6
50°-60°	0.8	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1101.3	97.0
0°-40°	1127.4	99.3
0°-60°	1134.7	100.0
0°-90°	1135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1135.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7852	
5°	6586	548
15°	1491	451
25°	200	103
35°	38	26
45°	8	7
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267376

CATALOG NUMBER: P3AS13R209735DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7851.6
1°	7785.0
2°	7588.9
3°	7307.5
4°	6962.3
5°	6585.5
6°	6165.7
7°	5702.4
8°	5161.9
9°	4626.3
10°	4066.3
11°	3470.3
12°	2875.2
13°	2371.1
14°	1889.1
15°	1491.1
16°	1176.9
17°	928.4
18°	746.0
19°	606.6
20°	497.9
21°	416.3
22°	347.5
23°	288.9
24°	241.0
25°	200.1
27.5°	130.9
30°	90.1
32.5°	55.5
35°	38.2
37.5°	24.4
40°	16.9
42.5°	11.5
45°	8.0
47.5°	5.3
50°	2.7
52.5°	1.3
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1267376

CATALOG NUMBER: P3AS13R209735DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)